



C-Kure Cut-Resistant Gloves



Frequently Asked Questions:

What is the ASTM 1790-04 rating of C-Kure Cut-Resistant Gloves? Level 5

Do C-Kure Cut-Resistant Gloves have anti-bacterial feature? Yes, Alphasan

Do C-Kure Cut-Resistant Gloves have a USDA compliance certification? Yes, C-Kure Cut-Resistant Gloves comply with Food Contact 21CFR Guidelines for component materials

Are C-Kure Cut-Resistant Gloves puncture proof and cut-resistant? C-Kure Cut-Resistant Gloves are cut-resistant, not puncture proof.

What is the normal wear and tear duration of this glove? Depending upon the application, normal usage is anywhere from 4 - 8 months.

What is the proper maintenance of C-Kure Cut-Resistant Gloves? See Laundering Instructions below.

Laundering Instructions:

- Gloves may be loaded directly into washer. Laundry bag not necessary, but acceptable.
- Water temperature should not exceed 180°F.
- Use of commercial laundry soap or detergent is acceptable.
- Bleach may be used on white product to restore whiteness. Bleach on grey product not necessary.
- Tumble dry at moderate temperature for approximately 10 minutes.
- Avoid temperatures in excess of 160°F and/or extended drying times.
- Overheating will cause shrinkage.**